

# Professional Ultrasonic Cleaner Skymen With Heater And Basket For Small Metal Parts 2.85 Gallon

### **Basic Information**

- Place of Origin:
- Brand Name:
- Certification:
- Model Number:
- Minimum Order Quantity:
- Price:
- Packaging Details:
- Delivery Time:
- Supply Ability:

JP-040S
1 unit
Negotiation
1unit per box
In Stock
8000 pcs per month

CE ROHS FCC SGS

China

Skymen



### **Product Specification**

<ul> <li>Model:</li> </ul>	JP-040S
<ul> <li>Frequency:</li> </ul>	40KHz
Capacity:	2.85 Gallon
Tank Size:	12*9*6 Inch
Ultrasonic Power:	120W/240W
<ul> <li>Heating Power:</li> </ul>	200W
Material:	SUS 304
• G.W:	8.4KG
<ul> <li>Highlight:</li> </ul>	30min Timer Ultrasonic Parts Cleaners, Bench Top Ultrasonic Cleaner SUS304, SUS304 Ultrasonic Cleaning Equipment



# for more products please visit us on skymenultrasonic.com

Our Product Introduction

# More Images



### **Product Description**

Professional Ultrasonic Cleaner Skymen With Heater And Basket For Small Metal Parts 2.85 Gallon

# **PAY ATTENTION ON DETAILS**



### Insulated handle design Anti-static and anti-high temperature, more secure







Stainless steel drain valve One-half inch large drain valve, quicker to drain



## **Cooling vents**

Fast heat dissipation, protecting the circuit board and enhancing the service life








Heat - resistant power cord

One-half inch large drain valve, quicker to drain









Model	Capacity	Tank Size	Ultrasonic Power	Heating Power	Frequency	Tank thickness	Material
	(L)	(L*W*H)mm	(W)	(W)	(KHz)	(mm)	SUS304
JP-008	0.8	150*85*65	35	0	40	1	SUS304
JP-009	0.9	150*135*65	60	100	40	1	SUS304
JP-010T	2	150*165*100	60	100	40	1	SUS304
JP-020S	3.2	240*135*100	120	100	40	1	SUS304
JP-030S	4.5	300*150*100	180	200	40	1	SUS304
JP-031S	6.5	300*150*150	180	200	40	1	SUS304
JP-040S	10	300*240*150	240	200	40	1	SUS304
JP-060S	15	330*300*150	360	300	40	1	SUS304
JP-080S	22	500*300*150	480	500	40	1	SUS304
JP-100S	30	500*300*200	600	500	40	1	SUS304
Product Show:							

Product Show:


3

) HEATING SYSTEM

Built-in heating board,You can adjust the heating water temperature from 20 to 80°C. It's efficient to remove oil and wax


Heating board














**Application Area:** 

# **MULTIPURPOSE CLEANING**

It's efficient for most of household items that could be used to clean. get the best cleaning effects with the least effort.







# COMPARISON OF CLEANING EFFECT



























# Suitable for varieties of palces





Labs

Factory

Hardware store





Model	Capacit y	Tank Size	Transducer s	Ultrasonic Power	Heating Power	Tank thickness	Frequency
	(L)	(L*W*H)mm	(pcs)	(W)	(W)	(mm)	(KHz)
JP-120ST	38	500X300X250	12	600	1500	2	28/40
JP-180ST	53	500X350X300	18	900	1500	2	28/40
JP-240ST	77	550X400X350	24	120	3000	2	28/40
JP-300ST	99	550X450X400	30	1500	3000	2	28/40
JP-301ST	99	800X300X400	30	1500	3000	2	28/40
JP-360ST	135	600X500X450	36	1800	4500	2	28/40
JP-480ST	175	700X500X500	48	2400	6000	2	28/40
JP-600ST	264	800X600X550	60	3000	6000	2	28/40
JP-720ST	360	1000X600X600	72	3600	9000	2	28/40
JP- 1108ST	540	1000X900X600	108	5400	18000	2	28/40
JP- 1144ST	960	1200X1000X800	144	7200	27000	2	28/40

Immersible Transducer Plate Image:



Model	Plate Size	Transducer s	Ultrasonic Power	Generator	Suitable tank
	(L*W*H)mm	(pcs)	(W)	(set)	(L)
JP-1006I	305*205*100	6	300	1	10~15
JP-1012I	355*305*100	12	600	1	30~40
JP-1018I	340*280*100	18	900	1	60~70
JP-1024I	430*280*100	24	1200	1	70~80
JP-1030I	460*370*100	30	1500	1	90~100
JP-1036I	550*450*100	36	1800	1	130~140
JP-1048I	600*450*100	48	2400	2	170~180

Immersible Transducer Tube Image:



Model	Tube Size	Transduce rs	Ultrasonic Power	Generat or	Length of wire	
WOUEI	(D*H)mm	(pcs)	(W)	(set)	(M)	
JM-1003	57*180	3	150	1	1.5	
JM-1006	57*300	6	300	1	1.5	
JM-1012	57*550	12	600	1	1.5	
JM-1018	57*750	18	900	1	1.5	
JM-1024	57*1000	24	1200	1	1.5	
JM-1036	57*1520	36	1800	1		

Immersible Transducer Plate/tube can be put in any tank, but it doesn't have heating function.

The price of tube is much higher than plate, Ultrasonic Tube is only used for special purpose, such as in Lab.

RFQ

Q: How to control the cleaning time?

A: Generally, 3minutes is enough for daily goods clean.

Q: Does ultrasonic cleaner damage the articles?

A: Ultrasonic cleaning is considered safe for most parts; although in some cases it is necessary to observe caution. Although the effect of thousands of implosions per second is very powerful, the cleaning process is safe.

Q: What about after-sale service?

A: our company provides 1 Year warranty. If any technical problem during warranty time, replacement parts will be sent free of charge. After warranty time, technical support is also available for every customer.

Q: What kind of cleaning solution should I use?

A: A large variety of different formulas designed for specific applications. Proper selection is crucial for acceptable cleaning activity and to prevent unwanted reactions with the work piece.

skymen Technology Corporation Limited

🔇 86-755-27094405 🖸 info@skymen.cc 😢 skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen